

LUMOTAST 75 IP40, signal lamps, rectangular collar, flat bezel,
Solder terminal

DISCONTINUED



Description

The LUMOTAST 75 IP 40 signal lamps have proven themselves over decades. The well-known connection and labeling concept make the LUMOTAST 75 IP 40 series your reliable component. These signal lamps offer protection class IP 40 according to DIN.



technical data

> general

Collar color	black
Collar shape	rectangular
Operating temperature, min.	-25 °C
Operating temperature, max.	55 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
illuminated	Yes
Lamp socket	T4.5
Packaging	Box
Packaging unit	10 pcs.
net weight	7.7 g
Degree of protection, front side, according to DIN EN 60529	IP40
Minimum order quantity (MOQ)	20 pcs.
RoHS compliant	Yes
REACH compliant	Yes
country of origin	HU

direct links

> RAFI eCatalog

> mounting diameters


Outside dimension, length	24 mm
Outside dimension, width	18 mm
Outside dimension, height	41 mm
Mounting hole	16.2 mm
Mounting depth	33.5 mm
Installation height	7.5 mm

> mechanical data

Fixing	Threaded ring
Solderability	Yes
Terminal on the rear	Solder terminal

drawings

Dimensioned drawing



Mounting hole drawing

