




Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1487596-1
USB, A-B, 28/24, BLACK, 2.0M



TE Part # 1487595-2
USB, A-B, 28/26, BLACK, 1.3M




TE Part # 292336-1
Std USB Type A, Flag, T/H



TE Part # 5353929-1
Std USB Type A, R/A, SMT, Offset, Panel



TE Part # 5787617-1
RECP ASSY, R/A, STACKED, THRU-HOLE, USB,




TE Part # 1487595-1
USB, A-B, 28/26, BLACK, 1.0M



TE Part # 1734366-1
Std USB Type A, VT, T/H

Customers Also Bought



TE Part #3870033006
44A1111-20-9-9



TE Part #1SNG609014R0000
ENBR-WG-M32-BL-A



TE Part #CQ50583001
LWB-101-3.0(10)




TE Part #TAD14747101-002
M12D4-MS-MS-FRNC TYPE B GREEN-1.0M



TE Part #0004-058-100L
CONT PIN




TE Part #1-66425-2
III+ PIN,30-26,TIN,STRIP



TE Part #CAT-P592-K742
PIDG Knife Disconnect Splices



TE Part #1-770834-1
MINI UMNL SOK PHBRZ AU LF



TE Part #1996706-1
8 POS VITA 67.2 RF MODULE, BACKPLANE,SMPM

Documents



Product Drawings

USB, A-B, 28/26, BLACK, .83M

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1487595-3_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1487595-3_M.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1487595-3_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.