

Representative Image

Catalog No. 18RAD-18277

Description: NYL FULLY INS FEM-187 DISC, 22-18

UPC No 786210818924

Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect

Nylon-Insulated Female Disconnect, Length .89 Inches, Width .30 Inches, Maximum Insulation .150, Tab Size .187x.020 Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

Descriptors

Category	Wire terminal disconnect
Special Features	Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.

Specifications

Material	Brass
Finish	Tin Plated
Color	Red
Insulation	Nylon/Polyamide

Classifications

Brand Name	Sta-Kon
Standard	UL E66716

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially isolated
Colour insulation	Red
Material insulation	PA
Material	Copper
AWG-range	22-18

by ABB

Downloaded from Arrow.com.

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622701	N/A	N/A	N/A
CSA	7222	622701	N/A	N/A	N/A
UL	E66716	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.