Part Number : 1727040059
Product Description : FCT Standard-Density Waterproof D-Sub Connector, Male, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, Plastic Watertight Frame, 9 Circuits, Red Insulator
Series Number : 172704
Status : Obsolete
Product Category : D-Sub Connectors
Engineering Part Number : FWDR09PA



Documents and Resources

Drawings

1727040059_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	D-Sub Connectors
Series	172704
Description	FCT Standard-Density Waterproof D-Sub Connector, Male, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, Plastic Watertight Frame, 9 Circuits, Red Insulator
IP Rating	IP67
Magnetic	Yes
Product Name	FCT Products
Type	Standard Density
UPC	889056019705

Electrical

Current - Maximum per Contact	7.5A
Shielded	Yes

Physical

Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Red
Durability (mating cycles min)	500
Gender	Male
Material - Contact	Copper Alloy
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Shell	Brass
Net Weight	5.400/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton

Obsolete

Downloaded from Arrow.com.

Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	No
PCB Retention	No
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Contact	Gold over Nickel Phosphorus
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shell Size	1
Temperature Range - Operating	-25° to +70°C
Termination Style	Solder Cup
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Size (AWG)	20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Standard Density D-Sub, Size 1, 9 Position, Socket

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub Dust Caps

Obsolete

Downloaded from Arrow.com.