



Part Number : [190750015](#)
Product Description : InsulKrimp Star Ring Tongue
Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton
Series Number : 19075
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : SRB-229-08X



Documents and Resources

Drawings

[190750015 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19075
Description	InsulKrimp Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal
UPC	800753079663

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin

Net Weight	0.717/g
Packaging Type	Carton
Stud Size	8 (M4)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	4.45mm
Wire Size (AWG)	14, 16

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640011900</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640051900</u>

This document was generated on Jun 04, 2026