

Part Number : 1210120118
Product Description : mPm DIN Base, Form A-18mm, B31 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket
Series Number : 121012
Status : Obsolete
Product Category : Industrial Connectors
Engineering Part Number : B312P11N0

Documents and Resources

Drawings

1210120118_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Obsolete

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Connectors
Series	121012
Description	mPm DIN Base, Form A-18mm, B31 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	883906719609

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Form	A - 18mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	Straight

Obsolete

Downloaded from Arrow.com.

Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire Size (AWG)	N/A

Obsolete

Downloaded from Arrow.com.