



## Ratchet P-Clamp

For bundle diameters from 12.7 mm to 19.5 mm

| TYPE       | Width (W) | Length (L) | Bundle Ø min. | Bundle Ø max. | Hole Ø (FH) | Fixing Hole Centres (F) | Variant     | Material            | Colour     | Article-No. |
|------------|-----------|------------|---------------|---------------|-------------|-------------------------|-------------|---------------------|------------|-------------|
| RCB90SM6   | 34.9      | 101.9      | 12.7          | 19.5          | M6          | 26.7                    | 90° Short   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01651   |
| RCB90SM8   | 34.9      | 101.9      | 12.7          | 19.5          | M8          | 26.7                    | 90° Short   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01457   |
| RCB180SM6  | 34.9      | 116.2      | 12.7          | 19.5          | M6          | 52.8                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01645   |
| RCB180SM8  | 34.9      | 116.2      | 12.7          | 19.5          | M8          | 52.8                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01440   |
| RCB180SM10 | 34.9      | 116.2      | 12.7          | 19.5          | M10         | 52.8                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01390   |
| RCB180SM12 | 34.9      | 116.2      | 12.7          | 19.5          | M12         | 52.8                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01441   |
| RCB90LM6   | 34.9      | 129.9      | 12.7          | 19.5          | M6          | 26.7                    | 90° Long    | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01652   |
| RCB90LM8   | 34.9      | 129.9      | 12.7          | 19.5          | M8          | 26.7                    | 90° Long    | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01460   |
| RCB180MM6  | 34.9      | 138.2      | 12.7          | 19.5          | M6          | 74.8                    | 180° Medium | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01646   |
| RCB180LM6  | 34.9      | 167.2      | 12.7          | 19.5          | M6          | 103.8                   | 180° Long   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01647   |

All dimensions in mm. Subject to technical changes.

For bundle diameters from 19.4 mm to 36.0 mm

| TYPE       | Width (W) | Length (L) | Bundle Ø min. | Bundle Ø max. | Hole Ø (FH) | Fixing Hole Centres (F) | Variant     | Material            | Colour     | Article-No. |
|------------|-----------|------------|---------------|---------------|-------------|-------------------------|-------------|---------------------|------------|-------------|
| RCC90SM6   | 34.9      | 141.8      | 19.4          | 36.0          | M6          | 39.9                    | 90° Short   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01659   |
| RCC90SM8   | 34.9      | 141.8      | 19.4          | 36.0          | M8          | 39.9                    | 90° Short   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01492   |
| RCC180SM6  | 34.9      | 156.1      | 19.4          | 36.0          | M6          | 62.3                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01653   |
| RCC180SM8  | 34.9      | 156.1      | 19.4          | 36.0          | M8          | 62.3                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01474   |
| RCC180SM10 | 34.9      | 156.1      | 19.4          | 36.0          | M10         | 62.3                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01475   |
| RCC180SM12 | 34.9      | 156.1      | 19.4          | 36.0          | M12         | 62.3                    | 180° Short  | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01476   |
| RCC90LM6   | 34.9      | 169.8      | 19.4          | 36.0          | M6          | 39.9                    | 90° Long    | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01660   |
| RCC90LM8   | 34.9      | 169.8      | 19.4          | 36.0          | M8          | 39.9                    | 90° Long    | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01495   |
| RCC180MM6  | 34.9      | 178.1      | 19.4          | 36.0          | M6          | 84.3                    | 180° Medium | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01654   |
| RCC180LM6  | 34.9      | 207.1      | 19.4          | 36.0          | M6          | 113.3                   | 180° Long   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01655   |

All dimensions in mm. Subject to technical changes.

For bundle diameters from 36.0 mm to 51.0 mm

| TYPE       | Width (W) | Length (L) | Bundle Ø min. | Bundle Ø max. | Hole Ø (FH) | Fixing Hole Centres (F) | Variant    | Material            | Colour     | Article-No. |
|------------|-----------|------------|---------------|---------------|-------------|-------------------------|------------|---------------------|------------|-------------|
| RCD180SM8  | 34.9      | 181.5      | 36.0          | 51.0          | M8          | 70.0                    | 180° Short | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01499   |
| RCD180SM10 | 34.9      | 181.5      | 36.0          | 51.0          | M10         | 70.0                    | 180° Short | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01501   |
| RCD180SM12 | 34.9      | 181.5      | 36.0          | 51.0          | M12         | 70.0                    | 180° Short | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01502   |
| RCD90LM8   | 34.9      | 195.2      | 36.0          | 51.0          | M8          | 42.4                    | 90° Long   | PA66HIRHSUV, ST, ZN | Black (BK) | 151-01521   |

All dimensions in mm. Subject to technical changes.

## Accessories

| TYPE      | Variant        | Material    | Colour     | Article-No. |
|-----------|----------------|-------------|------------|-------------|
| RCTT      | No Serration   | PA66HIRHSUV | Black (BK) | 151-01529   |
| RCINSERTA | Rubber profile | TPE         | Black (BK) | 151-01530   |
| RCINSERTB | Rubber profile | TPE         | Black (BK) | 151-01531   |
| RCINSERTC | Rubber profile | TPE         | Black (BK) | 151-01532   |
| RCINSERTD | Rubber profile | TPE         | Black (BK) | 151-01533   |

All dimensions in mm. Subject to technical changes.