Part Number : 1300960059
Product Description : Safeway Wire Mesh Grip, Straight Male, Cable Diameter 7.62-10.92mm (.300-.430"), Eye Dimension 1 11/16"
Series Number : 130096
Status : Active
Product Category : Cable Grips
Engineering Part Number : 36550



Documents and Resources

Drawings

1300960059_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:a8b6af20-e731-45d8-9f93-e8688a3aac82
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130096
Description	Safeway Wire Mesh Grip, Straight Male, Cable Diameter 7.62-10.92mm (.300-.430"), Eye Dimension 1 11/16"
Product Name	Safeway
Type	Strain Relief Grip
UPC	78678836550

Agency

CSA	LR32159

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	7.62-10.92mm (.300-.430")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	N/A
Net Weight	11.793/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.