

Han 24M HBM-Rear Fit-DL-w/o frame



Image is for illustration purposes only. Please refer to product description.

Part number	09 37 024 0392
Specification	Han 24M HBM-Rear Fit-DL-w/o frame
HARTING eCatalogue	https://harting.com/09370240392

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® M
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Rear mounting
Type	Low construction

Version

Size	24 B
Locking type	Double locking lever
Field of application	Hoods/housings for rough environments

Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)

Page 1 / 2 | Creation date 2025-10-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric Stiftung & Co. KG | Wilhelm-Hartung-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Material properties

Material (seal)	FPM
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	166 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140171343
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466