

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST
GP	00


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A8	ADD NEW DASH NUMBERS 1-1 AND 1-2	11JAN2022	CZ	SH
	A9	ADD NEW DASH NUMBERS 1-3 AND 1-4	27NOV2024	VNB	RCG
	A10	ADD NEW DASH NUMBER 1-5	19JAN2026	PK	VNB
	A11	ADD NEW DASH NUMBER 1-6	12MAY2026	PK	VNB






SHOULDER SCREW



COMPRESSION SPRING



FLAT WASHER

1. ONE(1) KIT CONSISTS OF TWO(2) EACH OF EACH PART SHOWN.
2. BULK PACKAGED. KITS TO BE ORDERED IN MULTIPLES OF 100.
3. SHOULDER SCREW: STAINLESS STEEL
   COMPRESSION SPRING: MUSIC WIRE
   FLAT WASHER: STAINLESS STEEL
4. (A11) SHOULDER SCREW: CARBON STEEL
   COMPRESSION SPRING: MUSIC WIRE
   FLAT WASHER: STAINLESS STEEL

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±.005
4 PLC	±.0020
ANGLES	±2°

MATERIAL - (3)

FINISH -

DWN	17MAR2013 P BRANDBERG
CHK	21MAR2013 M.CORRELL
APVD	-
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-

TE Connectivity

NAME
HARDWARE KIT
PANEL MOUNT MULTI BEAM
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1600914	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 2 | REV A11

1470-19 (3/11)

Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

A11	△4 Ø.24	.500	.854	1.104	△1 KIT, STANDARD SPRING	1-1600914-6
A10	△3 Ø.24	.500	.854	1.104	△1 KIT, STANDARD SPRING	1-1600914-5
A9	△3 Ø.364	.405	.854	1.004	△1 KIT, STANDARD SPRING	1-1600914-4
A9	△3 Ø.24	.405	.854	1.004	△1 KIT, STANDARD SPRING	1-1600914-3
	△3 Ø.24	.500	.854	1.104	△2 BULK, LOW FORCE SPRING	1-1600914-2
	△3 Ø.24	.500	.854	1.104	△1 KIT, LOW FORCE SPRING	1-1600914-1
	△3 Ø.24	.500	.854	1.104	△2 BULK, LOW FORCE SPRING	1-1600914-0
	△3 Ø.24	.500	.854	1.104	△1 KIT, LOW FORCE SPRING	1600914-9
	△3 Ø.24	.405	.854	1.104	△2 BULK, STANDARD SPRING	1600914-8
	△3 Ø.24	.405	.854	1.104	△1 KIT, STANDARD SPRING	1600914-7
	△3 Ø.24	.500	.644	.894	△2 BULK, STANDARD SPRING	1600914-6
	△3 Ø.24	.500	.644	.894	△1 KIT, STANDARD SPRING	1600914-5
	△3 Ø.24	.500	.854	1.104	△2 BULK, HIGH FORCE SPRING	1600914-4
	△3 Ø.24	.500	.854	1.104	△1 KIT, HIGH FORCE SPRING	1600914-3
	△3 Ø.24	.500	.854	1.104	△2 BULK, STANDARD SPRING	1600914-2
	△3 Ø.24	.500	.854	1.104	△1 KIT, STANDARD SPRING	1600914-1
	DIM. D	DIM. C	DIM. B	DIM. A	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±.005
4 PLC	±.0020
ANGLES	±2°

MATERIAL -

FINISH -

DWN P BRANDBERG 17MAR2013

CHK M.CORRELL 21MAR2013

APVD - -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

TE Connectivity

NAME
HARDWARE KIT
PANEL MOUNT MULTI BEAM
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1600914	-

CUSTOMER DRAWING

SCALE 4:1 SHEET 2 OF 2 REV A11

1470-19 (3/11)

Downloaded from Arrow.com.