



**Part Number :** [02092116](#)  
**Product Description :** 2.36mm Diameter,  
Standard .093" Pin and Socket Crimp  
Terminal, Series 1380, Male, with Tin (Sn)  
Plated Brass Contact, 22-18 AWG, Reel  
**Series Number :** 1380  
**Status :** Active  
**Product Category :** Crimp Terminals  
**Engineering Number :** 1380-(P901)  
**Packaging Alternative :** 02092118 (Bag)




Documents & Resources

**Drawings**  
[002092116\\_sd.pdf](#)

**Specifications**  
[PS-02-09-001.pdf](#)  
[PS-43660-9999-001.pdf](#)  
[11890000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	1380
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 22-18 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Standard .093"
UPC	800753760004

#### Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.323/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	N/A

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

## Use with Part(s)

Description	Part Number
Standard .093" Pin and Socket Dual Row Connector Housings	<u>1261</u>
Standard .093" Pin and Socket 3 Row Connector Housings	<u>1292</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1396</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1490</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1545</u>
Standard .093" Pin and Socket Single Row Connector Housings	<u>1619</u>

## Application Tooling

### Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	<u>11020003</u>
Extraction Tool for Standard .093" Pin and Socket Terminals	<u>11030006</u>
Extractor Tool for .093 and HCS-125 Product Series	<u>638240200</u>
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 18 AWG	<u>638280900</u>
Hand Crimp Tool for .093" Pin and Socket Crimp Terminals, 22 AWG	<u>638281400</u>
Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 20 AWG	<u>638281700</u>
Mini-Mac Applicator for Standard .093" Pin and Socket Terminals, for 22-18 AWG Wire with Insulation Diameter no greater than 2.29mm MAX	<u>638924000</u>

Mini-Mac Applicator for Standard .093" Pin and Socket Terminals, for 22-18 AWG Wire with Insulation Diameter no greater than 3.05mm MAX	<u>638927000</u>
---	------------------

---

This document was generated on Apr 22, 2025