





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

4-40thread(UNC)

4X THUMBSCREW






Amphenol Cables on Demand



D-SUB
15PIN Male

D-SUB
15PIN Male



PIN OUT:

Male	Male	Color
PIN1	PIN1	Black
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN4	Orange
PIN5	PIN5	Yellow
PIN6	PIN6	Green
PIN7	PIN7	Blue
PIN8	PIN8	Purple
PIN9	PIN9	Gray
PIN10	PIN10	White
PIN11	PIN11	Pink
PIN12	PIN12	Light Green
PIN13	PIN13	Black/White
PIN14	PIN14	Brown/White
PIN15	PIN15	Red/White
SHIELD	SHIELD	Drain Wire

LENGTH

LENGTH & P/N Table

LENGTH	P/N	Cable Color
2.5FT ±1 inch	CS-DSDMDB15MM-002.5	GREY
5FT ±2 inch	CS-DSDMDB15MM-005	GREY
10FT ±3 inch	CS-DSDMDB15MM-010	GREY
15FT ±3 inch	CS-DSDMDB15MM-015	GREY
25FT ±4 inch	CS-DSDMDB15MM-025	GREY
50FT ±8 inch	CS-DSDMDB15MM-050	GREY

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		07/Feb/2007	
A1	Add wiring color		13/JAN/2012	
A2	Revise cable specification (Delete bracket)		9/May/2016	



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	ANGLES
X ±X	±X°
XX ±XX	
.XXX ±.XXX	



THIRD ANGLE PROJECTION

EAR NO.	DATE
APPROVALS	
DRAWN LF	9/Nov/2016
CHECKED BA	9/Nov/2016
RESP ENG	

Amphenol Cables on Demand
20 VALLEY ST. ENIDCOTT, NY 13760
Deluxe 15PIN D-Sub MM

SIZE	DWG. NO.	REV.
A	CS-DSDMDB15MM-XXX	A2

NOTES: UNLESS OTHERWISE SPECIFIED

4

3

2

1

A

A

B

B

4

3

2

1