

**Part Number :** [936000043](#)

**Product Description :** Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg29 Thread

**Series Number :** 93600

**Status :** Active

**Product Category :** Heavy-Duty Cable Glands

**Engineering Part Number :** 7000.6845.0




---

## Documents and Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland, with Washer and Gaskets, Pg29 Thread
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 18.00, 21.00, 24.00, and 27.00mm internal diameters.
IP Rating	IP66
Product Name	Heavy-Duty Connectors
UPC	887191826158

### Physical

Cable Diameter	17.50-26.50mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel (body), Zinc (washer)
Material - Washer	Steel
Net Weight	59.000/g
Packaging Type	Bag
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg29
Thread Type	(Pg)

## Mates With / Use With

### Use with Part(s)

Description	Part Number
-------------	-------------

Use With	Enclosures Size A and B metal type
----------	------------------------------------

---

This document was generated on May 22, 2026