
Specification Sheet

Part Number: TAG73T1-795



Metalized polyester has a matte finish, allowing for the highest resolution and print contrast.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.

Thermal Transfer Adhesive Label, 2.0 x 1.0", 1 Across, Polyester, Silver, 3000/roll

Article Number	596-73795
Type	TAG73T1
Color	Silver (SR)
Quantity Per	pack
Product Description	HellermannTyton's metalized polyester labels include a layer of metallic particles that give the appearance of being made of metal. Applications include asset tracking and product rating plates. The high operating temperature makes them suitable for use on electronic equipment. Great for replacing expensive metal stampings, engravings and even silk screened rating plates, the printed labels offer high quality imaging for text and graphics and can be permanently placed on a wide variety of flat surfaces.
Short Description	Thermal Transfer Adhesive Label, 2.0 x 1.0", 1 Across, Polyester, Silver, 3000/roll

Downloaded from Arrow.com.

Global Part Name	TAG73T1-795-SR
Width W (Imperial)	2.0
Width W (Metric)	50.8
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Width of Liner (Metric)	55.88
Width of Liner (Imperial)	2.2
Material	Type 795, Polyester (795)
Material Shortcut	795
Adhesive	Acrylic
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)

Downloaded from Arrow.com.

Operating Temperature	-67°F to +302°F (-55°C to +150°C)
BABA Compliant	YES
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.