
Part Number : 1300350015
Product Description : Mini-Change Gender Changer, Straight Male/Male, 5 Poles
Series Number : 130035
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 115060A



Documents and Resources

Drawings

1300350015_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130035
Description	Mini-Change Gender Changer, Straight Male/Male, 5 Poles
IP Rating	IP67
Product Name	Mini-Change
Type	Gender Changer
UPC	78678848003

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	50V

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Orientation	Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire Size (AWG)	N/A

Downloaded from Arrow.com.