

D-Subminiature

500-008

Protective Cover, Panel Mount



500-008

This accessory fits D-Subminiature M24308 and Series 28 HiPer-D connectors.

Metal cover for panel-mounted connectors. 500-008 aluminum cover fits M24308 D-Subminiature and Series 28 HiPer-D connectors. Variable height cover completely shrouds connector and seats against panel. Optional EMI panel gasket. Supplied with standard 4 inch (102mm) attachment. Cover has silicone gasket to protect connector face. Cover is supplied with 4-40 male screwlocks to mate with M24308/26 female screwlocks on panel connector. Also available with female screwlocks for use with cable mounted connectors. Aluminum body, passivated SST screwlocks, and silicone gasket.

TABLE 1
SCREWLOCK OPTIONS

No Designator Fillister Hd Male	A Socket Hd Male	H Hex Head Male
J Female	K Slotted Knurled	

PART NUMBER																															
Sample PN →	500-008 M 3 R3 G A T 01 -4																														
Base P/N	500-008																														
Finish	TZ Tin-Zinc MN Mega-Nickel JF Cadmium, Yel. Chromate M Electroless Nickel NF Olive Drab Cadmium MT Nickel-PTFE ZR Black Zinc-Nickel																														
Shell Size	1 2 3 4 5 6																														
Cover Height	Omit for front mounted connector. Omit for Female Screwlocks (Code J). Rear Panel Mounted Connector <table border="1"> <thead> <tr> <th>Code</th> <th>Panel Thickness</th> <th>Cover Height</th> </tr> </thead> <tbody> <tr> <td>Omit</td> <td>N/A</td> <td>.344 (8.7)</td> </tr> <tr> <td>R1</td> <td>.031 (0.8)</td> <td>.187 (4.8)</td> </tr> <tr> <td>R2</td> <td>.047 (1.2)</td> <td>.171 (4.3)</td> </tr> <tr> <td>R3</td> <td>.062 (1.6)</td> <td>.156 (4.0)</td> </tr> <tr> <td>R4</td> <td>.093 (2.4)</td> <td>.125 (3.2)</td> </tr> <tr> <td>R5</td> <td>.104 (2.6)</td> <td>.114 (2.9)</td> </tr> <tr> <td>R6</td> <td>.125 (3.2)</td> <td>.093 (2.4)</td> </tr> <tr> <td>R7</td> <td>.156 (4.0)</td> <td>.062 (1.6)</td> </tr> <tr> <td>R8</td> <td>.138 (3.5)</td> <td>.080 (2.0)</td> </tr> </tbody> </table>	Code	Panel Thickness	Cover Height	Omit	N/A	.344 (8.7)	R1	.031 (0.8)	.187 (4.8)	R2	.047 (1.2)	.171 (4.3)	R3	.062 (1.6)	.156 (4.0)	R4	.093 (2.4)	.125 (3.2)	R5	.104 (2.6)	.114 (2.9)	R6	.125 (3.2)	.093 (2.4)	R7	.156 (4.0)	.062 (1.6)	R8	.138 (3.5)	.080 (2.0)
Code	Panel Thickness	Cover Height																													
Omit	N/A	.344 (8.7)																													
R1	.031 (0.8)	.187 (4.8)																													
R2	.047 (1.2)	.171 (4.3)																													
R3	.062 (1.6)	.156 (4.0)																													
R4	.093 (2.4)	.125 (3.2)																													
R5	.104 (2.6)	.114 (2.9)																													
R6	.125 (3.2)	.093 (2.4)																													
R7	.156 (4.0)	.062 (1.6)																													
R8	.138 (3.5)	.080 (2.0)																													
EMI Panel Gasket	G Gasket Included <i>Omit if not required</i>																														
Screwlocks (Table 1)	Omit Fillister Head Male Screwlocks A Socket Head Male Screwlocks H Hex Head Male Screwlocks J Female Screwlocks (<i>fixed, non-rotating</i>) K Knurled Slotted Head																														
Protective cover is supplied with standard 4 inch attachment: SST wire rope with blue nylon jacket (Type F) and .182" diameter ring. Use the attachment codes below to modify or delete the attachment.																															
Attachment Type (Table 2)	Omit for standard attachment L No Attachment See Table 2 for Attachment Types																														
Attachment Diameter	Omit for standard attachment. Omit for Attachment Type SK. <table border="1"> <thead> <tr> <th>Code</th> <th>Ring Diameter</th> </tr> </thead> <tbody> <tr> <td>01</td> <td>.140 (3.6)</td> </tr> <tr> <td>02</td> <td>.182 (4.6)</td> </tr> <tr> <td>04</td> <td>.197 (5.0)</td> </tr> <tr> <td>06</td> <td>.125 (3.2)</td> </tr> </tbody> </table>	Code	Ring Diameter	01	.140 (3.6)	02	.182 (4.6)	04	.197 (5.0)	06	.125 (3.2)																				
Code	Ring Diameter																														
01	.140 (3.6)																														
02	.182 (4.6)																														
04	.197 (5.0)																														
06	.125 (3.2)																														
Attachment Length	Omit for standard attachment. Length in One Inch Increments (Example: -5 for five inch length)																														

D-SUBMINIATURE ACCESSORIES