



Pushing Performance
Since 1945

D-Sub, MA AWG 20-24 crimp cont



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 000 8576
Specification	D-Sub, MA AWG 20-24 crimp cont
HARTING eCatalogue	https://harting.com/09670008576

Identification

Category	Contacts
Series	D-Sub
Identification	Standard
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section (mm²)	0.25 ... 0.52 mm²
Conductor cross-section (AWG)	AWG 24 ... AWG 20
Contact resistance	≤10 mΩ
Stripping length	4.5 mm
Performance level	1 acc. to CECC 75301-802

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	100
Net weight	0.147 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140087293
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522