
APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/18	
A		UPDATE DRAWING	11/2/18	AY/LW
B		UPDATE DRAWING	12/25/18	AY/DH



SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Red
Contacts: Copper Alloy
Plating:
Tin over nickel underplate overall
Electrical:
Current rating: 1.0 AMP
Contact resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding: 500V AC/DC
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

Positions: 04 thru 26
A = .050 [1.27] x No. of Positions + .133 [3.37]
B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	3/19/18
CHECKED	LW	3/19/18
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: .100 [2.54] IDC CONNECTOR MALE, ON WIRE TYPE, TIN PLATED

SIZE	PART NO.	REV.
X	MPH-XX-F3-T	B

REF: S00111C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.