


Industrial Power Strip 1580 Series

15A | 125V | 5-15R Outlets

Features



- Designed for power distribution in a compact area.
- Available with a single on/off switch, no switch or individually switched receptacles.
- The individually switched receptacles help eliminate Phantom Power. Save hundreds of dollars off your energy bill by switching individual devices off at the source.

Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug type available is NEMA 5-15P straight blade.
- Includes 15 Amp, 125 VAC circuit breaker to prevent accidental overload.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.
- UL/cUL recognized Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14 & CSA C22.2 No. 0.4-04
- TAA compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.

Plug Types



5-15P Straight Blade



On/Off Switch Part No.	Illuminated Light Only Part No.	Overall Dimensions			Outlet Qty	Outlet NEMA Type	Cord Length (ft)	Plug Type	Plug NEMA Type
		Height	Width	Length					
1580H10A1	1580T10A1	2.50	3.50	10.44	10	5-15R	6	Straight	5-15P
1580H10B1	1580T10B1	2.50	3.50	10.44	10	5-15R	15	Straight	5-15P

Data subject to change without notice

