

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212070001](#)
Status: **Active**
Overview: [mPm® DIN Valve Connectors](#)
Description: mPm® DIN Valve Connector, Form A, External Threads, 2 Pole Plus Ground with C3 Circuit, 24V, Red LED, Transparent Nitrile Gasket



Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-121207-S28-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121207](#)
Form A
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm® DIN Valve Connectors](#)
Product Name mPm®
Type Field Attachable Connector
UPC 883906711580

Physical
Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs Yes
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 26.308/g
Orientation 90° Angle
Pitch - Mating Interface 18.00mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 24V

Material Info
Engineering Number S28200TC320R

Reference - Drawing Numbers
[Packaging Specification](#) PK-121207-S28-001
[Product Specification](#) PS-121201-001-001, STR-1251-001
[Sales Drawing](#) SD-121207-001

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per
-ED/01/2017 (12
January 2017)
Halogen-Free
Status
Low-Halogen
**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[121207](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION