

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192150045

Status:

Active

Overview:

Splices

Description:

VersaKrimp Butt Splice for 4 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19215
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Butt, VersaKrimp
UPC	800755062656
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	14.092/g
Packaging Type	Bag
Temperature Range - Operating	149°C
Wire Size AWG	4
Electrical	
Voltage - Maximum	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	F-364
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19215-007



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per

January 2019)

Not Contained

Halogen-Free

Not Contained

Status

Not Contained

Low-Halogen

Not Contained

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19215 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192900007
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
Hand Crimp Tool	640013900
Square “DIN” style dies for 4 AWG	640037870

This document was generated on 09/19/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION