

BOX MOUNT D-SUB CONNECTORS



Obsolete

TE CONNECTIVITY (TE)

AMPLIMITE,R/A RCPT ASY,109,ZN,3

AMPLIMITE | AMPLIMITE , Commercial Pin & Socket

1757838-3

TE Internal Number: 1757838-3

Mil-Spec: M24308/23-33Z

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

Connector Style Receptacle

Post Diameter .76 mm [.03 in]

PCB Mounting Orientation Right Angle

Power/Signal/Coax Combination No

Number of Positions 25

PRODUCT DRAWING

English

3D PDF

DOCUMENTATION

Product Drawings

RECEPTACLE ASSEMBLY,AMPLIMITE,RT ANGLE, SERIES 109,SIZE 1 THRU 5

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Receptacle

PCB Mounting Orientation Right Angle

Shell Size 3

Terminates To Printed Circuit Board

Blindmate No

Product Type Connector

Configuration Features

Power/Signal/Coax Combination No

Number of Positions 25

Body Features

Non-Magnetic No

Shell Plating Material Zinc

Insert Arrangement MS18275-1

Shell Material Steel

Contact Features

Contact Size 20

Contact Mating Area Plating Material Gold

Contact Base Material Brass or Beryllium Copper

Contact Type Socket

Termination Features

Termination Post Length 3.95 mm [.156 in]

Mechanical Attachment

Mounting Hole Diameter 3.05 mm [.12 in]

Dimensions

Post Diameter .76 mm [.03 in]

Operation/Application

ULTRA-LITE Connector No

Industry Standards

NASA Qualification No

Packaging Features

Packaging Method Package

Other

Comment "Z" is stamped on connectors following M24308 part number as required. "Z" designates zinc shell plating.

Statement of Compliance

Statement of Compliance

PDF
