


REV.	DATE	DESCRIPTION
NC	03/28/00	INITIAL RELEASE
A	01/02/07	UPDATE DRAWING FORMAT

NOTE:
FLARE INTERNAL FLANGE TO $\varnothing 8.3 [.326] \pm 0.07$



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex						
7						DRAWN	G.R.S.						01/02/07	
6						CHECKED			PART DESCRIPTION BNC PANEL PLUG – 4 HOLE FLANGE —					
5						ISSUED								
4						SHEET	1 OF 1		PART NO. 112653					
3	CONTACT PIN	BRASS	GOLD	1	CAD FILE C:/112/112653.DWG			DWG. NO. 112653.DWG						REV. A
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	NICKEL	1	DO NOT SCALE DRAWING									
DESCRIPTION MATERIAL FINISH QTY														