

[United States](#) > [Government Solutions](#) > [All 3M Products](#) > [Industry and Professionals](#) > [Industrial Abrasives](#) > [Abrasives Product Catalog](#) > [Hand Pads, Rolls, Abrasive Sheets, and Sponges](#) > [Abrasive Sheets](#) > 3M™ Utility Cloth Sheet 314D, 9 in x 11 in P80 J-weight, 50 per inner 250 per case

3M™ Utility Cloth Sheet 314D, 9 in x 11 in P80 J-weight, 50 per inner 250 per case

3M ID: 60440106668 UPC#: 00051115197727

 Print  Share



An aluminum oxide abrasive product sheet constructed on a J weight, durable cloth backing.

- Durable
- Reduced shelling, even when torn or rolled

Need Help?

Questions? We can help [Contact Us](#)

OverviewDocuments

Specifications

Application Category	Adhesives, Coatings, Sealant Corrosion Removal , Blending/Deburring , Finishing/Polishing
Applications	Blending , Cleaning , Contour Finishing , Deburring , Rust Removal
Backing Material	Cloth
Backing Weight	J Weight
Brand	3M™
Coat Type	Closed Coat
Color	Maroon
Converted Form	Sheet
Equipment - Machines	Hand Sanding
Form Type	Utility
Grade	P80
Industries	Marine , Metalworking , MRO
Length	11 Inch
Length (Metric)	279.4 mm
Mineral Type	Aluminum Oxide
Position	Best
Primary Application	Metalworking , Paint Prep, Coating & Corrosion Removal
Product Form	Sheet
Sub Industries	Metal Fabrication
US Govt Contract Number	GS-21F-0075x
Width	9 Inch
Width (Metric)	228.6 mm

– Accessories



3M™ Sanding Block, Rubber, 05520, 2-3/4 in x 8 in, 10 per case