

Specification Sheet

Part Number: 151-00429



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval features and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Connector Clip, Panel Thickness 1.5-4.0mm, PA66HIRHS, Black, 500/pkg

Article Number	151-00429
----------------	-----------

Type	EC42
------	------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip, Panel Thickness 1.5-4.0mm, PA66HIRHS, Black, 500/pkg
Global Part Name	EC42-PA66HIRHS-BK
Length L (Imperial)	0.94
Length L (Metric)	24.0
Fixation Method	Edge Clips
Width W (Imperial)	0.53
Width W (Metric)	13.4
Height H (Metric)	18.0
Panel Thickness Min (Imperial)	0.06
Panel Thickness Max (Imperial)	0.16
Panel Thickness Min (Metric)	1.5
Panel Thickness Max (Metric)	4.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS

Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)
[RoHS/WEEE Compliance](#)
[Disclaimer](#)
[Terms and Conditions](#)