

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/10/10	
A		REVISED DIM.	10/25/10	



SPECIFICATIONS:

Material:

Insulator: Nylon 66 UL 94V-0

Insulator color: Natural

Electrical:

Operating voltage: 250 VAC

Current rating: 3 Amp max

Contact Resistance: 20 mohms max

Insulation resistance: 1,000Mohms MIN.

Dielectric withstanding voltage: 1,000V AC for 1 MIN.

Temperature Rating:

Temperature range: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 20

A = .098 [2.50] x No. of Spaces

B = .098 [2.50] x No. of Spaces + .154 [3.90]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	DY	2/10/10
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
SHROUDED CRIMP TERMINAL HOUSING

SIZE X	PART NO. 25CH-E-XX	REV. A
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1