



Color: white Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	50 m; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data	
Width	15 mm
Depth	0.2 mm
Strip width	15 mm

Mechanical data	
Mounting type	Sticking
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data	
Color	white
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Acrylic; permanent
Halogen-free	Yes
Weight	200 g
Fire load	0 MJ



Environmental requirements		
Ambient temperature (storage)		+10 ... +21 °C
Ambient temperature (operation)		-40 ... +150 °C
Relative humidity		40 ... 50 %

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4017332825191
Customs tariff number		39199080888

Product classification		
UNSPSC		55121612
eCl@ss 10.0		27-40-06-29
eCl@ss 9.0		27-40-06-29
ETIM 9.0		EC001288
ETIM 8.0		EC001288
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 210-702

↓

Documentation

Operating Instructions

2009-110 Information on printing material

1

28.08.2020

pdf

1190.09 KB

↓