

[Cable Assemblies](#) > [Copper Cable Assemblies](#) > [Power Cable Assemblies](#)

CA, BUSBAR MATING TO CORD END TML



✓ **ACTIVE**

OCP

TE Part # **2311291-1**

TE Internal #: **2311291-1**

Configuration : **Double-Ended**

Shielded : **No**


Color : **Black, Red**

Operating Temperature Range : **-25 – 125 °C**
[-13 – 257 °F]

Cable Assembly Type : **Power**

 [Add to List](#) ▼

[Similar Products](#)



ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America ▼

Request pricing, availability and customization options

CONTACT US



We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

CA, BUSBAR MATING TO CORD END TML

 [CA, BUSBAR MATING TO CORD END TML](#)

English

CAD Files

3D PDF

 [3D_CVM_CVM_2311291-1_1.pdf](#) 3D

Customer View Model

 [ENG_CVM_CVM_2311291-1_1.2d_dxf.zip](#)

English

 [ENG_CVM_CVM_2311291-1_1.3d_igs.zip](#)

English

 [ENG_CVM_CVM_2311291-1_1.3d_stp.zip](#)

English

Product Specifications

Application Specification

 [ENG_SS_114-152046_1.pdf](#) English

Product Specification

 [ENG_SS_108-152030_1.pdf](#) English

Qualification Test Report

 [ENG_SS_501-152045_1.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval

Downloaded from [Arrow.com](#). Drawing for all design activity.

Product Type Features	Shielded : No Cable Assembly Type : Power Connector Type (End A) : Crown Clip Junior Neutral Wire Size (AWG): 12 – 10
Configuration Features	Configuration : Double-Ended
Body Features	Color : Black, Red
Housing Features	Housing Material : LCP Housing Color : Black
Dimensions	Wire Size (AWG): 12 – 10
Usage Conditions	Operating Temperature Range : -25 – 125 °C [-13 – 257 °F]
Statement of Compliance	Statement of Compliance pdf

Compatible Parts

> [Contact Product Support](#)

Also in the Series

| [OCP](#)



Bus Bar Connectors
(2)



Power Cable
Assemblies (3)



Surge Arresters (21)

Events

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of
Sale

Suppliers

 Find Authorized Distributors

 What's New on TE.com

 Product FAQs

United States (EN)

Germany (DE)

China (中文)

Japan (日本語)

Find Your Country/Region ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2018 TE Connectivity. All Rights Reserved.