



Part Number : [39000128](#)

Product Description : Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Phosphor Bronze, 28-22 AWG, Reel

Series Number : 5558

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 5558-PBS2

Packaging Alternative : [39000129](#) (Bag)



Documents and Resources

Drawings

[039000128_sd.pdf](#)

[55580001-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[55560001-AS-000.pdf](#)

[55560002-AS-000.pdf](#)

[55560002-PS-CH-000.pdf](#)

[55560002-PS-ES-000.pdf](#)

[55560002-PS-SK-000.pdf](#)

[PS-5556-001-001.pdf](#)

[PS-5556-002-001.pdf](#)

[55560001-TS-000.pdf](#)

[55560010-TS-000.pdf](#)

[TS-5556-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5558
Description	Mini-Fit Male Crimp Terminal, Tin (Sn) Plated Phosphor Bronze, 28-22 AWG, Reel
Application	Wire-to-Wire
Product Name	Mini-Fit
UPC	800753827042

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.180/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housings	<u>5559</u>
Mini-Fit BMI Dual Row Plug Housings	<u>42475</u>
Mini-Fit Jr. Dual Row Plug Housings	<u>46993</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>11030044</u>
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 28-22 AWG	<u>638191000</u>
FineAdjust Applicator for Insulation Diameter	<u>639002700</u>

1.30-1.50mm, 28-22 AWG Wire	
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 28-22 AWG	<u>639020200</u>
FineAdjust Applicator for Insulation OD 0.95-1.08mm - 28-22 AWG	<u>639023800</u>
T2 Terminator for Insulation OD 1.30-1.50mm, 28-22 AWG	<u>639102700</u>
T2 Terminator for insulation OD 1.10-1.30mm - 28-22 AWG	<u>639120200</u>
T2 Terminator for Insulation Diameter 0.95-1.08mm, 28-22 AWG	<u>639123800</u>

This document was generated on Jun 09, 2026