

Downloaded from Arrow.com.





Material:

- Cable: UL20276 [30AWG(7/0.103 T.C)*1P INS:FO-SKIN +D.W(7/0.103 T.C)+AL/MY(spread) the Wiring)]x4C+30AWG(7/0.103 T.C)x1P INS:PP+28AWG(7/0.127)x5C INS:PP+ AL/MY+Drain Wire
 B.D(85%) PVC Jacket, OD: Ø5.6±0.2MM Color: Black(NK-K01).
- Connector: P1: HDMI 19P Male Contact: 15μ"; Nickel Plated Shell
 P2: DVI 18+1 Digital Male Contact: G/F, Nickel Plated Shell
- Shield: P1: Inner mold must be wrapped copper to connector shell & cable braid
 P2: Copper Foil 360° solder to connector shell & cable braid
- Hood P1&P2: Molded Type, PVC 45P, Color: Black (NK-K01)

Electrical:

- 100% Open Short & Mis Wire Test
- Contact Resistance: 3Ω Max
- Insulation Resistance: 10Ω Min
- Hi-Pot Voltage 300V DC

RoHS Complaint

Scale	1:1
TOLERANCE	
X.X	±0.40
X.XX	±0.25
X.XXX	±0.15
Angle	±3°

Modification	Date	Name

		Name
Drawn	12.07.11	Chappell
Approved		

ASSMANN WSW components

Item No. AK639-2-R

Title HDMI/M-DVI-D <=> D/M Cable, 2 Meters

Drawing No. rev00

Replace | Sheet