
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved







✔ Active

TE CONNECTIVITY (TE)

FASTON 375 REC FLAG 12-10 AWG TPBR LP

FASTON | 375

151791-2
TE Internal Number: 151791-2

EU RoHS Compliant
EU ELV Compliant

Terminal Type Receptacle

Wire Size (AWG) 12 – 10

Wire Size (mm^2) 3 – 6

Mating Tab Width 9.53 mm [.375 in]

Mating Tab Thickness 1.19 mm [.047 in]

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION —

Product Drawings

Flag Faston Recept Loose Piece
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminates To Wire & Cable
FASTON Yes
Insulated Wire Support Yes
Insulated No
Wire/Cable Type Discrete Wire
Wire Stop No
Wire/Cable Composition Stranded

Body Features

Plating Material Tin

Contact Features

Terminal Type Receptacle
Terminal Orientation Flag
Barrel Type Open
Crimp Type F-Crimp

Dimensions

Wire Size (AWG) 12 – 10
Wire Size (mm^2) 3 – 6
Mating Tab Width 9.53 mm [.375 in]
Mating Tab Thickness 1.19 mm [.047 in]
Accepts Wire Insulation Diameter Range 4.88 – 5.94 mm [.192 – .234 in]
Receptacle Stock Thickness .52 mm [.0205 in]
Wire Insulation Diameter (Max) 5.94 mm [.234 in]
Overall Length 22.94 mm [.903 in]

Industry Standards

UL Rating Listed

Packaging Features

Packaging Method Box
Packaging Quantity 500

Downloaded from Arrow.com.

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.