





- NOTES**
- ① MARK MANUFACTURER'S NAME, CATALOG LISTING, FED. MFG. CODE AND DATE CODE
 - ② 2X ELECTRICAL LEADS TO LAMPS: 20 GAGE PER MIL-W-81044/6
 - ③ 2X FILTERS: RED MS250101-13A
 - ④ 2X LAMPS: MS25237-327 (28 VOLTS)
 - 5 - MAXIMUM POWER CONSUMPTION PER LAMP TO BE 4.5 WATTS
 - 6 - TEE HANDLE: MATTE PLASTIC PER MIL-STD-395, PAINTED RED, COLOR NUMBER 31136 PER FED-STD-595
 - 7 - HANDLE MUST NOT APPEAR LIT UNDER AMBIENT LIGHT CONDITIONS AND MUST APPEAR LIT WHEN ENERGIZED UNDER AMBIENT LIGHT CONDITIONS
 - ⑧ TORQUE FASTENER 4 TO 6 IN-LB MAXIMUM AFTER INSTALLATION
 - 9 - CONTACTS SEALED PER MIL-PRF-8805 SYMBOL 3 (WATERTIGHT)

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.				
CHARACTERISTICS	ELECTRICAL DATA			
	CONTACT ARRANGEMENT			
	6X S P D T			
	LOAD (AMPS)	28 VDC		
		SEA LEVEL	50,000 FT	
		SILVER	SILVER	
		RESISTIVE	7	4
		INDUCTIVE	4	2.5
MOTOR	—	—		
OPERATING FORCE— — — — — 7 - 10 LBS				
OVERTRAVEL — — — — — .075 MIN				
TOTAL TRAVEL — — — — — .9 TYP				
FUNCTIONAL LAMP LIFE — 25 OPERATIONS MIN				


THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 01929

SWITCH - ENCLOSED

CATALOG LISTING
PH-130

THIRD ANGLE PROJECTION		
		
SCALE FULL		
DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACES	(.00)	±.015
THREE PLACES	(.000)	±.005
ANGLES		± 4°
WEIGHT 55 LB MAX		