

CT2248

DMM Probe Insulated Splice

Datasheet

Multimeter Probe Insulated Splice Two 4mm banana jacks Connect two...

Description

Digital Multimeter Probe Insulated Splice. Two 4mm banana jacks. Connect two sheathed banana plugs together.

- Materials: Body: Polyamide (Nylon); Contact: Brass, Nickel Plt.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT III
Current Max	36 A
Resistance Max	5 milliohms
Temperature (degrees)	-20 to +80 C
RoHS 2	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

