
463C6W

Industrial Connector

2CMA166906R1000



Connector, earthing sleeve position 6h, rated current 63A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Industrial Connector
Product ID	2CMA166906R1000
Function	Connector
EAN	73926966661
Catalog Description	Connector, 6h, 63A, IP67, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421743
E-Number Norway	1563883
E-Number Sweden	E2416418
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TC
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	63 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz|60 hertz
Degree of Protection	IP67|IP69
Cable Cross-Section	4...16 mm²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	108 millimetre
Product Net Height	112 millimetre
Product Net Length	286 millimetre
Product Net Depth	286 millimetre
Product Net Weight	0.88 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	0.88 kilogram
Package Length	158 millimetre
Package Units	box 1 piece

Downloaded from Arrow.com.