




Part Number : [555600307](#)
Product Description : 0.50mm Pitch SlimStack Plug, Surface Mount, Dual Row, Vertical, 1.50mm Stack Height, 30 Circuits
Series Number : 55560
Status : Active
Product Category : Board-to-Board Connectors



Documents & Resources


Drawings
[555600307_sd.pdf](#)

3D Models and Design Files
[555600307.dxf](#)
[555600307.pdf](#)
[555600307_stp.zip](#)

Specifications
[547220000-A00.pdf](#)
[SPK-55560-001-001.pdf](#)
[PS-54722-010-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	55560
Description	0.50mm Pitch SlimStack Plug, Surface Mount, Dual Row, Vertical, 1.50mm Stack Height, 30 Circuits
Series Name	0.5, BB H1.5
Application	Board-to-Board, Signal
Component Type	PCB Header
Product Name	SlimStack
UPC	800755973396

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Breakaway	No
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No

Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	1.50mm
Mated Width	6.00mm
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	41.270/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PC Tail Length	0.74mm
PCB Locator	No
PCB Retention	None
Pitch - Mating Interface	0.50mm
Shrouded	Fully
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.50mm Pitch Vertical SlimStack Receptacles	<u>54722</u>

This document was generated on Mar 09, 2025