



PRODUCT DETAILS

Find More Products

Request More Info

Part Number	NL8060BC21-11KG
Diagonal Size (in)	8.4
Pixel Resolution	800 x 600
Interface	LVDS
Display Mode	TN
Technology	a-Si
Display Module Size (mm)	200.0 x 152.0 x 10.1
Display Active Area (mm)	
Aspect Ratio	4:3
Backlight Luminance (nits)	750
LED Driver	104PW03F
Contrast Ratio	800:1
Viewing Angles (T/B/L/R)	80/80/80/80
Driver IC	
Response Time (ms)	18
Operating Temperature (°C)	-30 to 80
Touch Panel	PCAP
Others	

Representative Login

