




PRODUCT NUMBER	PITCH
HWxx30x000J0G	3.81 mm



2P-6P Ribs on both sides
7P-24P No rib



Material:

- Item ① Top body: Thermoplastic (UL94V-0)
- Item ② Bottom body: Thermoplastic (UL94V-0)
- Item ③ Terminal lever: Thermoplastic (UL94V-0) Orange (RAL2011/P)
- Item ④ Spring clamp: Stainless Steel
- Item ⑤ Female Contacts: PhBz (CuSn) Tin plated

Electrical

- Voltage rating: 300V
- Current rating: 8A
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

cULus

PART NO.: HW xx 3 0 x 0 00J0 G

N=Number of poles
Dim L=Nx3.81+0.80
Dim P=(N-1)x3.81

Poles	Dim L	Dim P
2P-6P	±0.20	±0.20
7P-12P	±0.25	±0.25
13P-18P	±0.30	±0.30
19P-24P	±0.40	±0.35

Solid block
No. of poles
02 2 poles
03 3 poles
...
24 24 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK						
ltr	ecn	no	dr	date	tolerances unless otherwise specified						title TERMINAL BLOCK					
					angles 	X.±0.5					SPRING CLAMP, PLUGGABLE PLUG					
						X.X±0.3										
						X°±1°					scale					
					dr	EVIN ZHONG	051514			dwg no		sheet 1 of 1		size		
					engr	EVIN ZHONG	051514			HWxx30x000J0G		A4				
					chr	HANKE FENG	051514									
					appd	SHI JUN	051514									
sheet index		revision sheet		A	1						type CUSTOMER Drawing					