

Home >

Downloads:

Series: Micro-Con-X [refresh](#)

Connector Type:

Coupling Style:

Contact Number:
contact arrangement

Contact Size: [i](#) only one option available

Contact Style:

Contact Gender:

Contact Plating: [i](#) only one option available

Rear Style:

Insert Material: [i](#) only one option available

Color Option: [i](#) only one option available

Wing Option: [i](#) only one option available

Part Number: **W17282-3PG-P-3ES**

UV resistant thermoplastic insert panel mount connector #20 solder cup 3-position pin (male) gold over nickel plating Insta-Click™ hex nut and gasket (with epoxy) no color option (standard black); No Wing (Standard)



Notes:

PC Tail sizes .280 and .335 are only available in #20 contacts.
Insta-Click™ connectors are only available in black UV resistant material
Winged coupling nuts are only available on cable-end connectors
Consult factory for optional threaded coupling
Consult factory for custom designed cable assemblies and connectors.

Switchcraft : 773-792-2700 | Conxall : 630-834-7504



sales@switchcraft.com

Home Support Contact Us Login