

San Ace

DC Fan San Ace 60

9HVA0612P1J0011

- Eco Products
- UL ratings
- CSA standards
- EN standards
- RoHS directive





- Specifications
- Download Materials List
- Applicable Models
- Related Information

Specifications

Model No.	9HVA0612P1J0011	Frame size [mm]	60
Frame thickness [mm]	38	Frame material	Plastic
Rated voltage [V]	12	Operating voltage range [V]	10.8 ~ 13.2
Rated current [A]	2.8	Rated input [W]	33.6
Rated speed [min-1]	24800	Max. airflow [m3/min]	2.39
Max. airflow [CFM]	84.3	Max. static pressure [Pa]	2000
Max. static pressure[inchH2O]	8.0	SPL [dB(A)]	68
Operating temperature[°C]	-20 ~ +70	Expected life[h]	40000/60°C (70000/40°C)
Mass [g]	130	Sensor type	Pulse sensor
PWM control function	Yes	Ribbed	No

Download Materials List












Login is required to download

Materials	Material No.	File Size	Download Link
Catalog			▶ Download 
Instruction Manual	M0011876B	906.5 KB	▶ Download 
CAD	9HVA_60x38_RBL	6.9 MB	Login required

Applicable Models

Model no.	Item Name
▶ 109-1003F13	Resin filter kit
▶ 109-1003F20	Resin filter kit
▶ 109-1003F30	Resin filter kit
▶ 109-1003F40	Resin filter kit
▶ 109-1003G	Resin finger guard
▶ 109-139E	Finger guard (Use for either inlet/outlet side)
▶ 109-139H	Finger guard (Use for either inlet/outlet side)

Related Information

▶ Airflow Tester Product Registration 
▶ San Ace Controller Product Registration 
▶ Software 
▶ Manual 
▶ Catalog Site 
▶ RoHS Directive compliance of your products 
▶ Fan Instruction Manual 
▶ Safety Precautions 
▶ Part Numbering System / The meaning of the specifications 
▶ Index by Model No. - DC Fans 
▶ Index by Model No. - ACDC Fans and AC Fans 
▶ Technical Information 
▶ Deleted models in this catalog 

Contacts