



Part Number : [1301020192](#)

Product Description : Super-Safeway Rubber Hand Lamp with 300W, Open End Guard with Reflector, with Receptacle

Series Number : 130102

Status : Active

Product Category : Lamps and Lights

Engineering Number : 115U



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Super-Safeway Rubber Hand Lamp with 300W, Open End Guard with Reflector, with Receptacle
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678860580

Agency

UL	E59251
----	--------

Electrical

Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	190.50mm (7.500")
Duty	Industrial
Guard Included	Yes
Guard Type	Open End, Reflector
Height	371.35mm (14.620")
Lamp Type	A23
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held

Outlet	Side
Packaging Type	Carton

This document was generated on Sep 11, 2025