



Part Number : 1301380095
Product Description : Watertite Outlet
Pendant Box, GFCI, (1) NEMA L5-20 Single
Receptacle with Flip Lid, 4.57m (15.0') Cord
Length, 12/3 SOOW Cord, Double Eye Wire
Mesh Cord Grip
Series Number : 130138
Status : Active
Product Category : Power Distribution
Engineering Number : 77W47M123GF



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Relevant

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130138
Description	Watertite Outlet Pendant Box, GFCI, (1) NEMA L5-20 Single Receptacle with Flip Lid, 4.57m (15.0') Cord Length, 12/3 SOOW Cord, Double Eye Wire Mesh Cord Grip
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA L5-20
Product Name	Watertite
Type	Single Outlet Box
UPC	78678810126

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	No
Voltage - Maximum	125V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	4.57m (15.0')
Cord Type	12/3 SOOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Net Weight	412.000/g
Number of Receptacles	1
Packaging Type	Carton
Receptacle Type	Single

This document was generated on Apr 19, 2025