Specifications



Photo is representative





Eaton HCM1104-R56-R

Eaton HCM1104 inductor, 0.56 uH, 25 A Irms, 32 A ISAT, 1.7 mΩ resistance, SMT mounting, Iron Powder, 2-pins, 850 qty.

General specifications	
PRODUCT NAME	Eaton HCM1104 inductor
CATALOG NUMBER	HCM1104-R56-R
UPC	051712544962
PRODUCT LENGTH/DEPTH	11.5 mm
PRODUCT HEIGHT	4 mm
PRODUCT WIDTH	10.3 mm
PRODUCT WEIGHT	2.49 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	25 A
ISAT	32 A
PACKAGE QUANTITY	850
MATERIAL	Iron powder
AUTOMOTIVE GRADE	No
FREQUENCY RATING	Up to 5 MHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-55 to 125 °C
RESISTANCE	1.7 mΩ
SIZE	11.5x10.3x4.0mm
TERMINALS	2 Pins
SERIES	HCM1104

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HCM1104-R56-R Eaton HCM 1104 high current power inductors data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.

Downloaded from Arrow.com.