

Part Number : 1301500144
Product Description : 20 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire, 250V, Orange
Series Number : 130150
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 420R12W

Documents and Resources

Drawings

1301500144_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130150
Description	20 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire, 250V, Orange
Comments	IEC Configuration 309-1/309-2
IP Rating	IP67
NEMA Configuration	N/A
Product Name	Watertite
Specialty	Pin and Sleeve
Type	Receptacle
UPC	78678870332

Agency

UL	E145923

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Type	N/A
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes

Downloaded from Arrow.com.

Poles	3-pole/4-wire
Receptacle Type	Single

Downloaded from Arrow.com.