

M12 Y-cod 8-pol st/st m/f PUR 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 262 7840 050
Specification	M12 Y-cod 8-pol st/st m/f PUR 5.0m
HARTING eCatalogue	https://harting.com/21342627840050

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 Y-coding Male Straight
Connector 2	M12 Y-coding Female Straight
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	8
Core structure	4x AWG20 + 1x 4x AWG26
Coding	Y-coding

Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight



Pushing Performance
Since 1945

Material properties

ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	760691ac-b4d2-427c-9996-5886190b813b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Country of origin	Czechia
European customs tariff number	85444995
GTIN	5713140282551
eCl@ss	27060390 Ready-made data cable (unspecified)
ETIM	EC002599
UNSPSC 24.0	26121600