




REV.	DATE	DESCRIPTION
NC	05/24/00	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



RECOMMENDED CABLE STRIPPING DIM'S



Amphenol Connex									
PART DESCRIPTION SMA 4-HOLE PANEL JACK (.141" SEMI RIGID - REVERSE POLARIZED)									
PART NO. 132108RP									
CAD FILE C:/132/132108RP.DWG									
DWG. NO.		132108RP.DWG		REV. A		SIZE A		SCALE NA	
APPROVALS		DATE							
DRAWN G.R.S.		07/20/05							
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm				UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"					
DO NOT SCALE DRAWING									
QTY									
FINISH									
MATERIAL									
DESCRIPTION									
1 BODY		1							
2 INSULATOR		1							
3 CONTACT PIN		1							
4									
5									
6									
7									
8									