


COAXIAL CONNECTOR, SMB, 50 Ohm, Straight cable plug (male)

11_SMB-50-1-40/111_N

Properties

- Snap-on mechanism provides a fast and reliable connection
- Ideal for applications with high packaging density
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
SMB	plug	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data	
Weight	0.0024 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165°C

COAXIAL CONNECTOR, SMB, 50 Ohm, Straight cable plug (male)

11_SMB-50-1-40/111_N

Ordering Information Table		
Item number	Item description	Packaging type
22648050	11_SMB-50-1-40/111_NE	Single
22650186	11_SMB-50-1-40/111_NH	Bulk 100 pcs

Suitable cables	
Cable group	U1 - 1 mm / 50 Ohm
Suitable cables	RG_178_B/U
	RG_196_A/U
	ENVIROFLEX_178

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3426 / Date of publication: 25.11.2023 / uncontrolled copy