


PANDUIT P/N	WEIGHT
FSTK	.2 LB/EA 90 g/EACH

NOTES:

1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESIS ARE METRIC.
3. TRAY WILL HOLD UP TO 6 MECHANICAL OR FUSION SPLICES.
4. INCLUDED WITH SPLICE TRAY:
 - 1 - CLEAR PLASTIC COVER
 - 1 - MECHANICAL SPLICE HOLDER
 - 1 - FUSION HOLDER
 - 5 - GREEN CABLE TIES
 - 5 - BLUE CABLE TIES
 - 1 - 6" PVC TUBE



MODEL FILENAME M00466AT_SPL_TRAJ_ASSY_00.PRT

CAD FILENAME/LAYERS M00466AT_DC_00A.PRT

PANDUIT
CORP. TINLEY PARK, ILLINOIS

SPLICE TRAY UNIT
6 MECHANICAL OR FUSION SPLICES
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
 $(.X) \pm .03$ $(.XXX) \pm .005$
 $(.XX) \pm .015$ ANGLES $\pm 1^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JDWE

DATE
5-2-02

MAT'L:

SEE NOTES

OTH

CHK'D

SCALE

NONE

DRAWING NO.

00466-67

DWG

A

SIZE

R 5-2-02 JDWE RELEASED TO PRODUCTION

REV DATE BY CHK

DESCRIPTION

ECN - R CUST SUP OTH