

Aptiv Connection Systems Catalog

Customer Service

Samples Request

Find by Feature

Browse by Category

Browse by Application

Comparison List (0)

Share

Enter part number or keyword

Search

Search Results (1)

Search Options

1 Result(s): [All] - 211PC062S5149

☐ Compare

211PC062S5149 - 6 Way 1.5mm
Female sealed NM SICMA
Connector green Generation 2

☐ Compare

6 Way 1.5mm Female sealed NM SICMA Connector green Generation 2

Part # 211PC062S5149



[Question about this product?](#)

Attributes	Documents (1)	Related Products (14)
Part # :	211PC062S5149	
Description :	6 Way 1.5mm Female sealed NM SICMA Connector green Generation 2	
Product Type :	Connector	
Status :	✓ Active	
Family :	Sicma	
Series :	1.5	
Cavities :	6	
Terminal(s) blade size [mm] :	1.5	
Sealable :	Sealed	
Gender :	Female	
Material :	PBT	
Weight [g] :	12	
Connector Color :	Green	
Remarks :	Former FCI Product, Delphi PN:10866615, Reduced size sealed housing - Sealing protection IP 71, Female part can be used as an aggregate housing, Circumferential interface seal, Rear sealing ensured by a pre-mounted mat-seal, Pre-assembled front grids support blade terminal guiding and mating, Terminal position assurance (T.P.A.) and connection position assurance (C.P.A.) option available, Acceptable wire size range from 0.5 to 2 mm ² for 1.5 mm and 0.5 to 4 mm ² for 2.8 mm	
Application :	Inline (Wire to Wire)	

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.