

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/2/19	


APPROVED: _____


DATE: _____ TITLE: _____





RECOMMENDED PCB LAYOUT





SPECIFICATIONS:
Material:
Housing: Nylon 66 Thermoplastic, rated UL 94V-2, Color: Natural
Contacts: Copper Alloy, ø0.16mm
Plating:
Tin over Nickel underplate overall
Electrical:
Current rating: 5A AC/DC
Voltage rating: 250V AC/DC
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM		ANGLE	
.X	± 0.35	X°	±2°
.XX	± 0.25	.X°	±1°
.XXX	± 0.15	.XX°	±0.5°

APPROVALS		DATE
DRAWN	OW	12/2/19
CHECKED	AC	12/2/19
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
MALE STRAIGHT, PCB MOUNT, 4P

SIZE	PART NO.	REV.
X	DDS-04D	-

REF: S00119T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.