



HD10 Series Housing for Female Terminals - 6 Cavities, Threaded Rear, No Coupling Ring

COM-15813 ROHS ✓

DESCRIPTION

FEATURES

DOCUMENTS

- Connector Style : Housing for female terminals
- Connector System : Wire-to-Wire
- Sealable : Yes
- Hybrid Connector : No
- Primary Locking Feature : Integrated in Housing
- Number of Positions : 6
- Nominal Voltage Architecture (V) : 12, 24, 42, 48, 80, 90, 125, 240
- Mating Pin Diameter : 2.5 mm [.098 in]

images are CC BY 2.0

 SHARE

COMMENTS 0

REVIEWS 0

Comments

 Looking for answers to technical questions?

We welcome your comments and suggestions below. However, if you are looking for solutions to technical questions please see our [Technical Assistance](#) page.

Log in or register to post comments.

 START SOMETHING.

Email address

SUBSCRIBE TO NEWSLETTER

ABOUT SPARKFUN

[Read Our Story](#)[Press & Media](#)[SparkFun Education](#)[Job Openings](#)

PARTNER WITH US

[See Our Partners](#)[Become a Distributor/Reseller](#)[Receive Volume Discounts](#)[Build a Custom Kit](#)[Apply for a Hardware Donation](#)

SUPPORT

[Customer Support](#)[Purchase Orders & Payment](#)[Terms](#)[Technical Assistance](#)[FAQs](#)[Contact Us](#)

SITE INFORMATION

[Terms of Service](#)[Privacy Policy](#)[Compliance](#)[Site Map](#)

SparkFun Electronics ® / 6333 Dry Creek Parkway, Niwot, Colorado 80503

Questions? Feedback? powered by [Olark live chat software](#)